


Titusoft EZ

Soft-closing mechanism for wooden drawers with roller runners

- Works with most roller runner drawer slides
- Designed for easy retrofit
- Intuitive positioning
- Controlled soft closing action



Technical details

Item number

973.0X35.380.00

- 100 Titusoft housings
- 100 activators

Bag of 1


973.0X35.380.K2

- 1 Titusoft housing
- 1 activator
- 2 screws Ø3.5mm x 20mm
- 2 screws Ø3.5mm x 12mm
- 1 Mounting instruction sheet

Bag of 2


973.0X35.380.K1

- 2 Titusoft housings
- 2 activators
- 4 screws Ø3.5mm x 20mm
- 4 screws Ø3.5mm x 12mm
- 1 Mounting instruction sheet



Made of plastic

Mounting procedure




Position the Titusoft housing with the posts resting on the top of the drawer slide and the front tab touching the cabinet side

Fix with 2 screws L=20mm

1. Rest the activator against the drawer front
2. Align the vertical position of the activator with the top of the Titusoft housing and mark the screw locations

Fix with 2 screws L=12mm

Mount 1 or 2 Titusoft housings depending on drawer weight and width → see details in capacity chart



A trial mounting is always recommended. Please contact Titus Group or your local distributor for further technical assistance.

Titus